


FLASHLIGHT

UFP-MDS-CC/HB



This **waterproof flashlight** version of the excitation light source allows a high level mobility in FP visualization. The new version has the interchangeability feature and can be used with all available light sources (**FS/ULS-02** models). The new light sources have the adjustable focus feature along with a 3 (three) position intensity switch. It operates on 4 (four) C size batteries. The **UFP-MDS-CC/HB** can be used for CFP, YFP, GFP, RFP and OFP emission visualization.



Light Source Model Number	Excitation Wavelength	Emission for Fluorescent Proteins
FS/ULS-02RB	440-460 nm	Cyan
FS/ULS-02B2	460-495 nm	Green & Yellow
FS/ULS-02G2	525-555 nm	Red
FS/ULS-02OR	567-588 nm	OrangeRed



BIOLOGICAL LABORATORY EQUIPMENT
MAINTENANCE AND SERVICE LTD.

www.bls-ltd.com

Zsélyi Aladár u.31, H-1165 Budapest, HUNGARY

Tel: +36-1-407-2602 Fax: +36-1-401-0925 E-mail: bls@t-online.hu Website: www.bls-ltd.com